## **Cornell Dubilier**

Cornell Dubilier Marketing, Inc Liberty, South Carolina TEL: 864-843-2277 FAX:864-843-3800

Engineering

Catalog Number: 101X303U040BB2A

Customer Part Number:

Date: 4/10/2019

Capacitance: 30000μF Tolerance: -10% +75% Working Volts: 40 VDC Surge Volts: 55 VDC

Leakage Current @ 25°C: <u>1643μA</u> ESR @ 120 Hz @ 25°C: <u>0.015Ω max.</u> Ripple Current @ 120 Hz, 85°C: <u>17.0A</u>

Diameter (D):  $2.00 \pm 0.031$  inches Length (L):  $3.125 \pm 0.062$  inches


Total Length, W/Insulation (TL):  $3.189 \pm 0.062$  inches

Terminal Spacing (S):  $0.875 \pm 0.015$  inches

Terminal Thread (T): 10-32 UNF

Insulation: PVC

Operating Temperature:  $-55^{\circ}\text{C} \sim +105^{\circ}\text{C}$ 



ROHS Compliant for all date codes after "0513", Per provisions of CD document 10-28.

"Controlled Copy" if viewed on CD Server or if copy is stamped in Red, Otherwise considered as an "Uncontrolled Copy"