

LTE CELLULAR
EXTENDER FOR
BUSINESS CONTINUITY



## **DIGIEX12**

Avoid network outages with primary or backup LTE connectivity; integrate seamlessly with existing infrastructure

Digi EX12 LTE cellular extender is an affordable, scalable failover solution that enables you to retrofit your infrastructure for cellular network access. With a carrier-certified, embedded LTE Cat 4 cellular modem, equipped with dual SIM slots, Digi EX12 provides uninterrupted primary or backup connectivity. It protects against downtime by automatically switching to a secondary cellular carrier should the primary SIM lose Internet access. This compact, high-performance device is also compatible with any dual-WAN networking appliance and helps you achieve reliable connectivity at any location using your existing equipment.

Couple the Digi EX12 with a dedicated wireline ISP connection to maximize uptime and ensure reliable network availability

for POS systems, ATMs, mobile kiosks, digital signage and more. Deployments are streamlined with installation accessories including mounting hardware, a disposable battery pack for site survey and a passive PoE injector for optimizing placement for the best cellular reception.

Digi EX12 can be securely monitored and managed with Digi Remote Manager®, a cloud-based solution that facilitates setup, mass configuration and support for Digi and third-party devices. Digi Remote Manager lets you evaluate, update and configure your Digi enterprise routers and gateways—and the health of your network—at scale, after deployment.

### **FEATURES AND BENEFITS**

- Redundant connectivity with dual SIMs and Digi SureLink™
- Optimized connectivity to any Ethernet device
- Built-in Digi TrustFence® for device security, device identity and data privacy
- Site survey battery pack to identify the best location for optimum cellular reception
- Remote mounting kit for quick, easy installation
- Automatic cellular carrier detection and switching with Carrier Smart Select™
- Digi Remote Manager software for easy setup, mass configuration and management

### **RELATED PRODUCTS**












Digi Remote Manager

# BACK OFFICE OR IN STORE BROADBAND MODEM (Cable/DSL ISP) POS TERMINAL DUAL-WAN CONNECTIVITY POWER OVER ETHERNET PRIVATE LAN GUEST WI-FI POOR CELLULAR RECEPTION GOOD CELLULAR RECEPTION

SPECIFICATIONS	DIGI® EX12	
CELLULAR CONNECTIVITY		
EX12-R004-OUS	LTE: B2, B4, B5, B12, B13, B14, B66, B71; 3G: B2, B4, B5; Transfer rate (max): 150 Mbps down, 50 Mbps up	
CONNECTORS	(2) 50 Ω SMA (center pin: female)	
SIM SLOTS	(2) Mini-SIM (2FF); software selectable and hardware switchable	
SOFTWARE AND MANAGEMENT		
REMOTE MANAGEMENT	Digi Remote Manager; SNMP v1/v2c/v3 (user installed/managed)	
LOCAL MANAGEMENT	RIP, RIPng, OSPFv2, OSPFv3, BGP, Babel, IS-IS	
MANAGEMENT/ TROUBLESHOOTING TOOLS	FTP client, SCP; protocol analyzer with PCAP for Wireshark; event logging with Syslog and SMTP client; NTP/SNTP	
MEMORY	256 MB RAM, 512 MB flash	
ETHERNET		
PORTS	(2) RJ-45; 10/100 Mbps (auto-sensing)	
SERIAL		
PORTS	(1) RS-232 (RJ-45)	
PHYSICAL		
DIMENSIONS (L x W x H)	127 mm x 127 mm x 25 mm (5.0 in x 5.0 in x 1.0 in)	
WEIGHT	0.24 kg (8.25 oz)	
STATUS LEDs	LAN (link = solid, flashing = act), WAN (link = solid, flashing = act), LTE, 5 signal	
ENCLOSURE	Plastic	
POWER REQUIREMENTS		
POWER INPUT	18 VDC 1 A	
OTHER	Remote mounting kit: temporary battery, passive PoE injector, mounting bracket and accessories	
ENVIRONMENTAL		
OPERATING TEMPERATURE	0° C to 40° C (32° F to 104° F)	
RELATIVE HUMIDITY	5% to 95% (non-condensing)	
APPROVALS		
CELLULAR	PTCRB; US: AT&T, Verizon, Canada	
EMISSIONS / IMMUNITY	FCC Part 15, Subpart B, Class A; CE, RCM; CAN ICES-3(B)/NMB-3(B)	
WARRANTY		
PRODUCT WARRANTY	3-year	

### **PRODUCT IMAGES**







### **DIGI REMOTE MANAGER®**



### **INFRASTRUCTURE**

- Hosted in a commercial-grade SAS 70-certified environment
- Superior availability, operating to 99.9% or greater
- Open APIs available to support application development

### **CAPABILITIES**

- Centralized management of remote devices over 3G/4G/LTE
- Define standard configurations and automatically monitor individual devices for PCI security compliance
- Get alerts and create reports on performance statistics, including connection history, signal quality, latency, data usage and packet loss
- No servers or applications to operate and maintain
- Perform tasks across your entire device network in minutes
- Edit configurations and update firmware for individual devices or groups
- Monitor the status and location of remote devices via a web browser
- Activate or deactivate cellular lines and monitor data to ensure you never incur overage charges

### **SECURITY**

- Certified SSAE-16 facilities
- Over 175 security controls in place to protect your data
- Enables compliance with security frameworks like PCI, HIPAA, NIST
- Earned SkyHigh's Cloud Trust Program highest rating of Enterprise-Ready

PART NUMBERS	DIGI EX12
EX12-R004-OUS	Digi EX12: 2-port 10/100; RJ-45, RS-232; US and Canada, LTE / HSPA+ Cat 4; Cellular certifications: PTCRB, AT&T, Verizon, Canada

PART NUMBERS	ACCESSORIES
450069	18 V PSU power supply with barrel jack connector (replacement)
500170	10/100 base-T passive PoE adapter, green (replacement)
440084	4 meter flat Cat 6 Ethernet cable, white (replacement)
440091	0.5 meter flat Cat 6 Ethernet cable, white (replacement)
560083	Temporary site survey battery pack, 9 V with 152.4 mm power lead, 2.1 mm barrel connector (replacement)

# FOR MORE INFORMATION PLEASE VISIT DIGI.COM



© 1996-2019 Digi International Inc. All rights reserved. All trademarks are the property of their respective owners. DIGI INTERNATIONAL WORLDWIDE HQ 877-912-3444 / 952-912-3444 / www.digi.com

DIGI INTERNATIONAL GERMANY +49-89-540-428-0

**DIGI INTERNATIONAL JAPAN** +81-3-5428-0261 / www.digi-intl.co.jp DIGI INTERNATIONAL SINGAPORE +65-6213-5380

**DIGI INTERNATIONAL CHINA** +86-21-50492199 / www.digi.com.cn

