

You Are Here: [Home](#) > > [SMA/SMA \(Sercos\) SERIES II POF Patch Cords](#) > **IF 637-1-5****SMA/SMA (Sercos) SERIES II POF Patch Cords, 1.50 m****SMA 905 connectors, 1.0 mm core, chemical-resistant 2.2 mm jacket**

Industrial Fiber Optics manufactures multiple product lines of premium quality fiber optic patch cords suitable for Sercos networking and other industrial networking applications. This particular cable series is for short distance applications such as those inside cabinets, those that require moderate tensile strength and others which must withstand moderate physical abuse and/or exposure to chemicals. These cables are more resistant to chemicals and have higher tensile strength than the IF 636 series cables. Patch cord consists of a fiber cable with industry-standard 1.0 mm optical core surrounded by a polyamide jacket with all stainless steel SMA 905 connectors. Equivalent to Allen Bradley 2090-SCNP and the Bosch Rexroth IKO0982 series. Available to all customers and OEM manufacturing companies as a direct purchase item.

Part Number: IF 637-1-5

- ◆ Polyamide 12 jacket for chemical resistance and cable strength
- ◆ Strain reliefs to minimize fiber stress at terminations
- ◆ 1 μ m polish terminations ensure high optical coupling efficiency
- ◆ Epoxied connector terminations for maximum retention strength
- ◆ Assembly processes exceed industry-standard procedures

Structure

			Unit	Value
Fiber Cable	GHN4001	Length	m	1.50 \pm 0.05
Connector One	SMA 905	Loss Typical (per term.)	dB	0.65
Connector Two	SMA 905 stainless	Loss Maximum (per term.)	dB	1.15
RoHS Compliant	No	Optical Loss	dB/m	.17 Max. @ 650 nm
		Operating Temperature	$^{\circ}$ C	-55 ~ 85
		Storage Temperature	$^{\circ}$ C	-55 ~ 85
		Fiber Tensile Strength	N	

RoHS Certification: No
Manufacturer's Datasheet