KENDALL HOWARD

V-RACKS - TAPPED RAILS





Kendall Howard V-Racks allow you to vertically or horizontally mount servers or other rackmountable devices regardless of depth. The V-Racks with 10-32 tapped rails are great for smaller rackmount equipment. Designed to mount on a wall or under a desk, the Kendall Howard V-Rack provides users more versatility on where they can place their products while saving them space.

- Low profile design
- Tapped rails
- Includes 10-32 Rack Screws
- No depth restrictions
- 150 lb. weight capacity
- Made in the USA
- Limited Lifetime Warranty

FEATURES

Low Profile Design - The V-Rack sticks out just a few inches from the wall. Mounting equipment like this is perfect for applications where space is at a premium.

No Depth Restrictions - The open design allows you to install servers, switches, and other network equipment regardless of depth.

Multiple Uses - Designed to mount to the wall, under a desk or to any surface to provide a 19" EIA compliant rail system. If you need a 4-point mounting system, simply mount two V-Racks back to back.

Tapped Rails - Tapped rails are great when mounting small rackmount equipment. This rail style is especially useful for one-time installations.

www.kendallhoward.com

KENDALL HOWARD







Size	2U - Tapped Rails	3U - Tapped Rails	4U - Tapped Rails
Part Number	1916-2-101-02	1916-2-101-03	1916-2-101-04
Width	19.25"	19.25"	19.25"
Depth	3.89"	5.64"	7.39"
Height	6"	6"	6"
Finish/Color	Black Powdered Coat Finish	Black Powdered Coat Finish	Black Powdered Coat Finish
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	FedEx Ground	FedEx Ground	FedEx Ground

4U

www.kendallhoward.com