KENDALL HOWARD

RACKMOUNT DRAWERS





The Kendall Howard Rackmount Drawer provides a secure space within your rack or cabinet for storing files, electronics, software, cables, testers, and more. By storing equipment within the rack, you'll save time running back and forth to retrieve it. Kendall Howard Rackmount Drawers include a built-in lock and have a maximum load capacity of 100 lbs.

FEATURES

Heavy Duty - The heavy gauge steel construction and attention to detail make this rackmount drawer capable of holding up to 100 lbs. Not only can you utilize the drawer but the top cover can double as a shelf for supporting more equipment.

Full Extension Ball Bearing Slides - The smooth ball bearing slides allow the drawer to be slid in and out with ease.

Four Mounting Holes Per U Space - Each rackmount space (U space) features four mounting holes so that the drawer can be securely installed. To maintain the maximum weight capacity, we suggest installing rack screws through every hole.

www.kendallhoward.com

KENDALL HOWARD =

4U





Size	2U	3U	4U
Part Number	1922-3-100-02	1922-3-100-03	1922-3-100-04
Width	19"	19"	19"
Depth	16.60"	16.60"	16.60"
Height	3.47"	5.22"	6.97"
Material(s)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)	CRS (Cold Rolled Steel)
Finish/Color	Black Powder Coat Finish	Black Powder Coat Finish	Black Powder Coat Finish
UPC	879447002164	879447002171	879447002188
Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty	Limited Lifetime Warranty
Shipping Method	FedEx Ground	FedEx Ground	FedEx Ground

www.kendallhoward.com