

LINIER® SWING-OUT WALL MOUNT CABINETS

AMERICAN
MADE 



The LINIER® Swing-Out Wall Mount Cabinets are designed to solve the everyday problems technicians have while installing and managing the immense amount of cabling that is all-too-common with datacom and telecom equipment. The LINIER® Swing-Out Wall Mount Cabinets are available with three different door options: glass, solid, and vented. All styles are reversible and can be left or right mounted to accommodate your particular installation. The glass door allows you to monitor your network system; the solid door helps secure and enclose your network system; and the vented door provides ventilation for your network system. Don't work around the rack...get a rack that works around you!

- Includes one locking door
- Locking side panels
- 150 lb. weight capacity
- One set of cage nut style mounting rails
- 90 degree positive stop swing-out
- Mounting depth: 22.50"
- 19" EIA 310-D compliant
- Made in the USA
- 5-Year Limited Warranty

FEATURES

Economical Design - Smartly engineered to include all the features you would expect, at a competitive price point, and with the quality that comes with American manufacturing.

90 Degree Swing-Out - Lockable enclosure can be swung out 90 degrees from the back frame allowing access to the rear of installed equipment. This capability provides additional space and accessibility for terminating, installing, and managing cables.

Numerous Laser Knockouts - Strategically placed laser knockouts provide a plethora of locations to feed copper or fiber optic cabling into the cabinet, or to install an optional fan kit for temperature control.

Adjustable Rails - The included cage nut style rails fully adjust in 1" increments to accommodate the various depths of equipment on the market. Additional rails are available for devices that require 4-point mounting.

Removable Side Panels - Easy to remove side panels provide more access for growing or changing cabling schemes, as well as offer the option for increased air flow to prevent equipment from overheating.

GLASS DOOR

SOLID DOOR

VENTED DOOR



6U



9U



12U



15U



18U



22U

Size	Dimensions	Glass Door	Solid Door	Vented Door
6U	23.50" W x 26.64" D x 14.21" H (Usable depth: 22.50")	3130-3-001-06	3131-3-001-06	3132-3-001-06
9U	23.50" W x 26.64" D x 19.46" H (Usable depth: 22.50")	3130-3-001-09	3131-3-001-09	3132-3-001-09
12U	23.50" W x 26.64" D x 24.71" H (Usable depth: 22.50")	3130-3-001-12	3131-3-001-12	3132-3-001-12
15U	23.50" W x 26.64" D x 29.96" H (Usable depth: 22.50")	3130-3-001-15	3131-3-001-15	3132-3-001-15
18U	23.50" W x 26.64" D x 35.21" H (Usable depth: 22.50")	3130-3-001-18	3131-3-001-18	3132-3-001-18
22U	23.50" W x 26.64" D x 42.21" H (Usable depth: 22.50")	3130-3-001-22	3131-3-001-22	3132-3-001-22