

## Energizer Vision HD + Focus LED Headlamp ENR HDD32E.5 NA HL WB VISION HD+FOCUS HL

Light your way out of even the darkest places with this innovative headlight, the lightweight, hands-free Energizer Vision HD+ Focus LED Headlamp. With its pivoting head for customizable, directional light, up to 85-meter beam, and IPX4 water-resistant construction, this durable headlamp is the ideal choice for any lover of the outdoors. Its thoughtful design lets you choose from 5 light modes, including night vision, and its red LED light makes it great for nighttime illumination, whether you're camping, hiking, or fishing. The digital focus of this LED headlight also allows you to seamlessly transition from spotlight to full flood light. The super comfortable and adjustable band fits a range of sizes, from kid to adult, and is completely washable. With advanced memory recall, you can quickly return to working with the last focus setting you used before powering off. Give a round of applause to our best hands-free Energizer Vision HD+ Focus LED Headlamp for all your adventures.

Country of Origin: CN | Material Number: E300277407 | Segment: Lighting

**Unit of Sale** 

**UPC:** 039800125231

**Dimensions (HxLxW):** 7.5 IN | 1.55 IN | 5.75 IN

**Volume:** 0.039 FT3 **Weight:** 0.26 LB

**Inner Carton** 

UPC: -

Dimensions (HxLxW): - IN | - IN | - IN

Volume:

Weight: - Units Per Inner: -

Case

**UPC:** 30039800125232

**Dimensions (HxLxW):** 6.0 IN | 9.13 IN | 3.87 IN

Volume: 0.123 FT3 Units Per Case: 4.000 Weight: 1.191 LB Inners Per Case: -

**Pallet** 

**Dimensions (HxLxW):** 47.0 IN | 48.0 IN | 40.0 IN

**Volume:** 52.222 FT3 **Weight:** 453.039 LB

Cases Per Layer: 50.000 Layers Per Pallet: 7.000 Cases Per Pallet: 350.000

## **Features & Benefits**

- Lightweight and comfortable Energizer Vision HD+ Focus LED Headlamp works with 3 Energizer MAX AAA batteries (batteries included)
- Powerful beam reaches up to 85 meters and puts out up to 400 lumens with its LED technology
- Switches easily between 5 light modes: high, low, full spot, full flood, and night vision (red) for outdoor illumination anytime, anywhere
- Pivoting headlight with Digital Focus conveniently allows the beam to adjust from wide-range to a focused beam
- This durable headlamp resists damage from drops up to 1 meter high, for worry-free use, whether you're hiking, biking, or working around the garage
- IPX4 water-resistant construction withstands splashing
- Runs for up to 3 hours in high mode

## **Light Specific Features:**

Lumens: High: 315 Low: 20

Beam Distance:

Runtime: High: Low: 50

Holdin