

ø42mm Planetary Gear Motor Brushless


MOT-I-81522

Online ID#:

PGMBL-HS42-24-80-67-C

Our BLDC Planetary Gear Motors are an inline solution providing excellent torque output and superior reliability and control.

With endless performance combinations, we have a fully tailored gear motor solution for you.





Specifications		
Gearhead Type:	Planetary	No-Load
Motor Type:	Brushless (SPM, 12 Pole)	No-Loa
Rated Voltage:	24V DC	Stall To
Rated Speed:	55 rpm	Max. Po
Rated Torque:	38 kg.cm	Reducti
Rated Current:	1.5 A	Termina

No-Load Speed:	67 rpm (+/- 10%)	
No-Load Current:	<500 mA	
Stall Torque:	210 kg.cm	
Max. Power:	36 W	
Reduction Ratio:	80:1	
Termination Style:	Molex (87439-0801)	

^{*} Gearbox limitations are set at 60 kg.cm, operating past this torque limit may create premature failure.

