

10ft CAT 6 Molded Snagless RJ45 UTP Networking Patch 24AWG Cable (Gray) E08-010



Micro Connectors' Category 6 cables eliminate cross talk between twisted pairs and staggered connectors to reduce near end crosstalk. The snagless connector works great for connecting workstations routers and network security devices.

Features:

- Molded boots (snagless installation) and extra protection for the RJ45 connector and clip
- UTP (Unshielded Twisted Pair) patch cable with 24 AWG (American wire gauge) stranded pure copper. Pure copper conductors provide the best signal possible
- Our Cat6 Ethernet patch cables exceed the EIA/TIA-568-C standard
- Designed specifically for Gigabit Ethernet applications
- RJ45 plug features gold connectors to prevent corrosion thus ensuring a longer cable life