
# Cabinet / Door Handles

Aluminum, with Tapped or Counterbored Through Holes







- 2 Type
- A Closed type
- Open-end type, mounting from the back (tapped blind hole)
- Open-end type, mounting from the operator's side

# Metric table

Dimensions in: millimeters - inches I<sub>1</sub> ±0.25 a<sub>1</sub> b<sub>1</sub>  $b_2$ d<sub>1</sub>  $d_2$  $h_4$ l<sub>3</sub> ±0.2 l<sub>4</sub> 16  $a_2$  $a_3$  $h_3$  $t_2$ min. 162 38 19 40 25 28 M 8 8.3 55 57 36 38 28 128 140 8 22 10 20 12 16 0.98 1.10 0.33 2.17 2.24 1.42 5.04 5.51 0.31 0.87 0.39 0.79 0.63 0.31 0.75 1.57 1.50 1.10 0.47

#### **Specification**

- Aluminum Powder coated Black, RAL 9005, textured finish
- SW Silver, RAL 9006, textured finish SR
- · Cover cap (Type C) Plastic
- Black (for SW)
- Light gray (for SR)
- Load Rating Information → page 2068
- RoHS compliant

# On request

· Various metric size fasteners and kit packaging

#### Information

3

GN 559 open-end or closed-end type cabinet / door handles are mainly used in applications requiring a sturdy and rugged grip.

A special characteristic of the GN 559 is the thumb rest pad on the front leg.

Because of the dual mounting holes, there is a choice of two center hole mountings on the closedend handle. Due to the dual mounting holes on the open-end handle, the handle is secured tightly into position after installation.

How to order  GN 559-162-B-SW	1 Length I <sub>1</sub>	
	2 Type	
	3 Finish	