

2ft Low Profile Angled Power Cord Extension, 16 AWG, 2-Pack M05-113LPA2-2P





Low Profile Angled NEMA 5-15P to NEMA 5-15R SJT 16 AWG.

- Extend the length of an existing power cord or outlet for more flexibility.
- Perfect design for indoor use in tight space, space-saving flat NEMA 5-15P connector.
- 45° angled 3-prong connector prevents blocking outlet space for other power connection.
- Ideal power supply extension for indoor appliances, computers, HDTV, printers, and more.
- The 16 AWG power cord is fully molded for durability.
- VW-1 105°C (221°F) and FT-2 105°C (221°F) temperature rating.
- UL and cUL listed.
- All relevant materials are complied with RoHS and REACH directives.

Connector A: NEMA 5-15P Low Profile Angled.

Connector B: NEMA 5-15R.
Conductor: SJT 16 AWG. x 3C.
Amp/Voltage Rating: 13A/125V.

Wattage Rating: 1625W.