

ø30mm Planetary Gear Motor Carbon - Brushed

MOT-I-81573-30-27

Online ID#:

PGM-30-6-27-408-C

Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.



Contact Us for alternative solutions!

Specifications	
Gearhead Type:	Planetary
Motor Type:	Carbon - Brushed
Rated Voltage:	6V DC
Rated Speed:	338 rpm
Rated Torque:	3 kg.cm
Termination Style:	Terminals

No-Load Speed:	408 rpm (+/- 10%)
No-Load Current:	< 1 A
Stall Torque:	19 kg.cm
Stall Current:	20 A
Max. Power:	20 W
Reduction Ratio:	27:1





