



SS Stainless Steel

**Inch table**

Dimensions in: inches - *millimeters*

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> Length l			d <sub>3</sub>	b	h <sub>1</sub>	h <sub>2</sub>
1.81 46.0	1/4 x 20	0.625 15.9	0.750 19.1	1.000 25.4	0.51 13.0	0.24 6.1	0.89 22.6	0.24 6.1
1.81 46.0	5/16 x 18	0.625 15.9	0.750 19.1	1.000 25.4	0.51 13.0	0.24 6.1	0.89 22.6	0.24 6.1
2.28 57.9	5/16 x 18	0.750 19.1	1.000 25.4	1.250 31.8	0.63 16.0	0.28 7.1	1.04 26.4	0.28 7.1
2.28 57.9	3/8 x 16	0.750 19.1	1.000 25.4	1.250 31.8	0.63 16.0	0.28 7.1	1.04 26.4	0.28 7.1

**Metric table**

Dimensions in: millimeters - *inches*

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> Length l			d <sub>3</sub>	b	h <sub>1</sub>	h <sub>2</sub>
46 1.81	M 6	16 0.63	20 0.79	25 0.98	13 0.51	6 0.24	22.5 0.89	6 0.24
46 1.81	M 8	16 0.63	20 0.79	25 0.98	13 0.51	6 0.24	22.5 0.89	6 0.24
58 2.28	M 8	20 0.79	25 0.98	30 1.18	16 0.63	7 0.28	26.5 1.04	7 0.28
58 2.28	M 10	20 0.79	25 0.98	30 1.18	16 0.63	7 0.28	26.5 1.04	7 0.28

**Specification**

- Stainless steel precision casting AISI CF-8  
Matte shot-blasted finish **MT**
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**On request**

- Special inch or metric threaded stud sizes

**Information**

The ridges on the wings of GN 835 wing screws permit a better grip.

see also...

- Wing Screws GN 431 (Stainless Steel) → page 679
- Wing Screws GN 433 (Stainless Steel) → page 678
- Hand Knobs GN 6335.5 (Stainless Steel) → page 632

**How to order**

<sup>1</sup> <sup>2</sup> <sup>3</sup> <sup>4</sup>  
**GN 835-2.28-3/8X16-1.25-MT**

- |   |                                |
|---|--------------------------------|
| 1 | Handle diameter d <sub>1</sub> |
| 2 | Thread d <sub>2</sub>          |
| 3 | Length l                       |
| 4 | Finish                         |

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

