

## STRIPPER/CUTTER - STRIPAX PRO 6



Cat No: PA1113 UPC No: 769328107968

Description

Now for THHN and THHW industrial insulations. The original stripax set the industry standard for precision stripping for a decade. The new stripax Pro 6 and Pro 16 perform powerful stripping of standard and industrial insulations for a wire range of 28-10 AWG (.08-6 mm2) and 10-6 AWG (6-16 mm2) respectively. The ergonomically designed, contoured handles let you hold the tool in a natural position so stripping is comfortable and requires less effort

Consistently strips heavy-duty and industrial insulations including THHN & THHW

Strips standard insulations including PVC, rubber and silicone

Provides nick-free stripping of insulation with no damage to conductors

Built-in cutter provides a smooth, straight cut without distorting the conductor

Fine adjustment slider on top of tool lets you adjust tothe insulation thickness

Handles designed for comfort and require low hand force

Not for Teflon® or Kapton hard insulations (use part number PA1115P mini-stripax Plus with a Teflon® blade for these insulations)

Perfect companion for any of our wire ferrule crimpers

Strippers carry a lifetime warranty

Blade warranty is one year for defects only

Teflon® is a registered trademark of DuPont.

## Specifications

Application: For THHN And THHW Industrial Insulations,

Handle Type : Contoured

Overall Length: 7.250 IN (185.000 MM)

Replacement Part : PA2113 stripax Pro 6 replacement stripping blade set

Stripping Range: 28 - 10 AWG (0.080 - 6.000 SQ-MM)

Sub Brand: stripax

Type: Pro 6

Weight: 5.500 OZ (156.000 GM)



Copyright © 2012 Greenlee Textron Inc., a subsidiary of Textron Inc. All rights reserved. | Powered by the Precis E-business Platform™