

PUNCH DRIVER ASSY, HYD KNOCKOUT (1732)

Driver with Ram, 3/8, 3/4 and 1-1/8 Punch and Die Adapters

Cat No: 1732

UPC No: 783310273615

## Description

- Fast, one-shot punching, nopredrilling of pilot holes
- Throat measures 8 IN (203 mm) deep
- Use with 1/2 IN through 4 IN conduit size and other round sizes only
- Use with Greenlee standardround punches and dies (optional)

## **Specifications**

- Capacity: Up Through 10 GA (3.000 MM) Mild Steel With Greenlee Standard Punches And Dies, 1/2 IN Through 4.000 IN Conduit
- Includes: "13266 UPC 13266 Punch Adapter 3/8 IN x 1/2 IN, 13267 UPC13267 Punch Adapter 3/4 IN x 1 IN, 13268 UPC 13268 Punch Adapter 1-1/8 IN, 11791 UPC 11791 Die Adapter 3/8"", 11790 UPC 11790 Die Adapter 3/4"", 11789 UPC 11789 Die Adapter 1-1/8"", 2733 "
- Type : Portable C Frame
- Weight: 59.000 LB (27.000 KG)