

37 MM PKG PNCH

Standard Slug-Splitter Knockout Punches



Cat No: 31122

UPC No: 783310311225

Description

 Slug-Splitter SC heavy-dutypunches are designed to punchup through 10 gauge (3.5 mm) stainless steel

- Unique slug-splitting design and tool steel constructioneasily punch 10 gauge (3.5 mm) mild steel and stainless steel
- Self-centering punch aligns itself on pilot hole. (Slug-Splitter SC)
- No need to draw crosshairsor line up die alignment marks
- (Slug-Splitter SC)
- Unique punch profile also splits slugs for easier slug removal
- Heavy-duty dies and stainless steel draw studs for longer life
- Excellent abrasion resistance for punching fiberglass and plastic
- · Slug-Splitter SC punch units consist of: punch, die and draw stud
- Check individual punch for specific capacity
- U.S. Patent No. 4,543,722for standard Slug-Splitter
- Patent Pending for Self-centering Slug-Splitter SC

Specifications

- Application : For Standard Slug-Splitter Knockout Punches
- Capacity Stainless Steel: 10 GA (3.500 MM)
- · Draw Studs:
 - 31872, 29452 Hydraulic Drivers
 - 12099 Ratchet Driver
- PG:29
- Size: 1.457 IN (37.000 MM)
- Type : Knockout