

DIE-RD 20,4MM PKGD

Standard Slug-Splitter Knockout Punches



## Image Unavailable

Cat No: 31129

UPC No: 783310311294

## Description

- Slug-Splitter SC heavy-dutypunches are designed to punchup through 10 gauge (3.5 mm) ٠ stainless steel
- Unique slug-splitting design and tool steel constructioneasily punch 10 gauge (3.5 mm) mild steel • and stainless steel
- Self-centering punch aligns itself on pilot hole. (Slug-Splitter SC) •
- No need to draw crosshairsor line up die alignment marks ٠
- (Slug-Splitter SC) ٠
- Unique punch profile also splits slugs for easier slug removal •
- Heavy-duty dies and stainless steel draw studs for longer life •
- Excellent abrasion resistance for punching fiberglass and plastic •
- Slug-Splitter SC punch units consist of: punch, die and draw stud
- Check individual punch for specific capacity ٠
- U.S. Patent No. 4,543,722 for standard Slug-Splitter •
- Patent Pending for Self-centering Slug-Splitter SC

## **Specifications**

- Application : For 0.803 IN (20.400 MM) (PG-13) Standard Slug-Splitter Knockout Punches ٠
- Capacity Stainless Steel : 12 GA (2.500 MM)
- Draw Studs : •
  - 29451, 29451 Hydraulic Drivers 0
  - 30227 Ratchet Driver 0
- Type : Round