



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™

DIE-RD 37,0MM PKGD

Standard Slug-Splitter Knockout Punches



Image
Unavailable

Cat No: 31135

UPC No: 783310311355

Description

Standard Slug-Splitter Knockout Punches

Specifications

- Application : For 1.457 IN (37.000 MM) (PG-29) Standard Slug-Splitter Knockout Punches
- Capacity Stainless Steel : 10 GA (3.500 MM)
- Draw Studs :
 - 31872, 29452 Hydraulic Drivers
 - 12099 Ratchet Driver
- Type : Round