

BIT, IMPACT 9/16 (.562) X18X.437 (37868)

Nail Eater Extreme Impact Bits

Cat No: 37868

UPC No: 783310378686

Description

Quickly bore through creosoted and salt-treated utility poles

- Resists wear, eats throughnails and staples
- Self-feeding screw point draws the bit through the wood
- 7/16 IN hex shank to fit impact drivers
- Available in 18 IN overalllength.

Specifications

Bit Diameter : 5/8 IN (15.900 MM)

Hardware Diameter: 9/16 IN (14.300 MM)
Overall Length: 18.000 IN (457.200 MM)
Shank Diameter: 7/16 IN (11.100 MM)

Shank Type : HexagonalSub Brand : Nail Eater

• Type : Extreme

Weight: 0.900 LB (409.000 GM)