

BIT, IMPACT 11/16 (.687) X18X.437 (37869)

Nail Eater Extreme Impact Bits

Cat No: 37869

UPC No: 783310378693

Description

Quickly bore through creosoted and salt-treated utility poles

- Resists wear, eats throughnails and staples
- Self-feeding screw point draws the bit through the wood
- 7/16 IN hex shank to fit impact drivers
- Available in 18 IN overalllength.

Specifications

Bit Diameter: 3/4 IN (19.100 MM)

Hardware Diameter: 11/16 IN (17.500 MM)
Overall Length: 18.000 IN (457.200 MM)
Shank Diameter: 7/16 IN (11.100 MM)

Shank Type : HexagonalSub Brand : Nail Eater

Type : Extreme

Weight: 1.100 LB (499.000 GM)