

BIT, NAILEATER 13/16 (.812) X 18.00(66PT)

Nail Eater Extreme

Cat No: 66PT-13/16

UPC No: 783310309253

Description

"Improved cutting edge provides 30% longer life span

- Patented new design for improved cutting and cleaner holes
- Self-feeding screw point draws bit through wood
- Unique patented design cutting angle smoother starts, reduced cutting loads
- Made of super tough, heat-treated steel
- cuts through nails and provides longer life
- ?Shorty"" bits for working in tight places, yet still can go through three abutting 2 x 4s
- See ?Bit Extensions"" if more length is required
- P.O.P packaged "

Specifications

Bit Diameter: 13/16 IN (20.600 MM)

• Material : Heat Treated Steel

Overall Length: 18.000 IN (457.200 MM)Shank Diameter: 7/16 IN (11.100 MM)

Shank Type : HexagonalSub Brand : Nail Eater

Twist Length: 15.000 IN (381.000 MM)

Type : Extreme

Weight: 1.200 LB (545.000 GM)