

BIT, NAILEATER 15/16 (.937) X 18.00(66PT)

Nail Eater Extreme

Cat No: 66PT-15/16

UPC No: 783310309291

Description

- "Improved cutting edge provides 30% longer life span
- Patented new design for improved cutting and cleaner holes
- Self-feeding screw point draws bit through wood
- Unique patented design cutting angle smoother starts, reduced cutting loads
- Made of super tough, heat-treated steel
- cuts through nails and provides longer life
- ?Shorty"" bits for working in tight places, yet still can go through three abutting 2 x 4s
- See ?Bit Extensions"" if more length is required
- P.O.P packaged "

Specifications

- Bit Diameter: 15/16 IN (23.800 MM)
- Material: Heat Treated Steel
- Overall Length: 18.000 IN (457.200 MM)
- Shank Diameter: 7/16 IN (11.100 MM)
- Shank Type : Hexagonal
- Sub Brand : Nail Eater
- Twist Length: 15.000 IN (381.000 MM)
- Type : Extreme
- Weight: 1.600 LB (726.000 GM)