



BIT, NAILEATER 1.00X18.00 (66PT-1)

Nail Eater Extreme

Cat No: 66PT-1

UPC No: 783310309314

## Description

- "Improved cutting edge provides 30% longer life span •
- Patented new design for improved cutting and cleaner holes •
- Self-feeding screw point draws bit through wood •
- Unique patented design cutting angle smoother starts, reduced cutting loads •
- Made of super tough, heat-treated steel •
- cuts through nails and provides longer life
- ?Shorty"" bits for working in tight places, yet still can go through three abutting 2 x 4s •
- See ?Bit Extensions"" if more length is required •
- P.O.P packaged "

## **Specifications**

- Bit Diameter : 1.000 IN (25.400 MM) •
- Material : Heat Treated Steel •
- Overall Length : 18.000 IN (457.200 MM) •
- Shank Diameter: 7/16 IN (11.100 MM)
- Shank Type : Hexagonal •
- Sub Brand : Nail Eater •
- Twist Length : 15.000 IN (381.000 MM)
- Type : Extreme
- Weight : 1.800 LB (817.000 GM) •