

DRIVER-RIGHT ANGLE HYD KO (7904E)

Metric Quick Draw 90 Driver, 2 Draw Studs, 1 Adapter, 1 Spacer and Case

Cat No: 7904-E

UPC No: 783310342991

Description

- Compact, lightweight designfor portability and fast, easy one-person operation
- Develops 8 tons of hydraulic force for easy punching, even in 10-gauge stainless steel, depending on individual punch capacities
- · Quick Draw is perfect for fast, straight-on front panel punching
- Quick Draw 90's right angle driver head rotates over 180degrees for maximum flexibility in tight working areas
- · Quick Draw Flex allows unlimited driver orientation to simplify access to work area
- Can be used with non-roundpunches within the capacity of the tool (adapter may be required)
- U.S. Patent #6,772,521

Specifications

- Includes: 33786 UPC 33786 Quick Draw Hydraulic Punch Driver, 1614SS UPC 30043 Draw Stud-3/8 IN x 2-13/16 IN, 31872 UPC 31872 DrawStud-3/4 IN x 4-1/8 IN, 1924AA UPC 03248 Spacer-Short, 33967 UPC 33967 Stud Adapter-3/8 IN, 35202 UPC 35202 Plastic Case
- Sub Brand : Quick Draw 90
- Type: Hydraulic, Metric
- Weight: 11.000 LB (5.000 KG)