

HOLESAW, VARIABLE PITCH (1 1/2")

Bi-Metal Hole Saws

Cat No: 825-1-1/2

UPC No: 783310191483

Description

• Cut through steel, tin, aluminum, fiberglass, wood and plastic

- Deep 1-5/8 IN (41.3 mm) cutting depth allows for cuttingthrough 2 IN x 4 IN wood studs
- Extra-tough bi-metal blade- we use the highest grade oftool steel to outlast competitor's blades. That beats premature saw replacement and savesyou money
- Steam oxide finish no paint to gum up and slow cutting. The saw runs cooler for longer life and better performance
- Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting
- Made in USA

Specifications

Cutting Size: 1-5/8 IN
Hole Diameter: 1-1/2 IN
Material: Bi-Metal
Pipe Tap Size: 1-1/4 IN
Type: Variable Pitch

Use With Quick Change Arbor No.: 2800
Use With Standard Arbor No.: 37156 Or 37154