GREENLEE。 MADE FOR THE TRADE!"



HOLESAW, VARIABLE PITCH (1")

Description

- Cut through steel, tin, aluminum, fiberglass, wood and plastic •
- Deep 1-5/8 IN (41.3 mm) cutting depth allows for cuttingthrough 2 IN x 4 IN wood studs •
- Extra-tough bi-metal blade- we use the highest grade oftool steel to outlast competitor's blades. • That beats premature saw replacement and savesyou money
- Steam oxide finish no paint to gum up and slow cutting. The saw runs cooler for longer life and better performance
- Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting •
- Made in USA

Specifications

- Cutting Size : 1-5/8 IN •
- Hole Diameter : 1.000 IN •
- Material : Bi-Metal
- Pipe Tap Size : 3/4 IN •
- Type : Variable Pitch ٠
- Use With Quick Change Arbor No. : 2800 •
- Use With Standard Arbor No. : 37157, 37155 Or 38522 •