

HOLESAW, VARIABLE PITCH (2 3/4")

Bi-Metal Hole Saws



Cat No: 825-2-3/4

UPC No: 783310191650

Description

• Cut through steel, tin, aluminum, fiberglass, wood and plastic

- Deep 1-5/8 IN (41.3 mm) cutting depth allows for cuttingthrough 2 IN x 4 IN wood studs
- Extra-tough bi-metal blade- we use the highest grade oftool steel to outlast competitor's blades. That beats premature saw replacement and savesyou money
- Steam oxide finish no paint to gum up and slow cutting. The saw runs cooler for longer life and better performance
- · Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting
- · Made in USA

Specifications

Cutting Size : 1-5/8 INHole Diameter : 2-3/4 INMaterial : Bi-Metal

Type : Variable Pitch

Use With Quick Change Arbor No.: 2801Use With Standard Arbor No.: 37156