

HOLESAW, VARIABLE PITCH (1 3/8) STD PK 30

Bi-Metal Hole Saws

Cat No: 825B-1-3/8

UPC No: 783310298328

Description

• Cut through steel, tin, aluminum, fiberglass, wood and plastic

- Deep 1-5/8 IN (41.3 mm) cutting depth allows for cuttingthrough 2 IN x 4 IN wood studs
- Extra-tough bi-metal bladewe use the highest grade of tool steel to outlast competitor's blades. That beats premature saw replacement and saves you money
- Steam oxide finish no paint to gum up and slow cutting. The saw runs cooler for longerlife and better performance
- Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting
- Made in USA

Specifications

Application : For 1.000 Conduit IN

• Cutting Size: 1-5/8 IN

D Chain : 4

Hole Diameter: 1-3/8 IN

Material : Bi-Metal

Material Master Number : 50298321

Package : 30/Standard Pack

• Type : Variable Pitch

Use With Quick Change Arbor No.: 2800

Use With Standard Arbor No.: 37156 Or 37154