

HOLESAW, VARIABLE PITCH (2 1/2) STD PK 30

Bi-Metal Hole Saws

Cat No: 825B-2-1/2

UPC No: 783310298366

Description

• Cut through steel, tin, aluminum, fiberglass, wood and plastic

- Deep 1-5/8 IN (41.3 mm) cutting depth allows for cuttingthrough 2 IN x 4 IN wood studs
- Extra-tough bi-metal bladewe use the highest grade of tool steel to outlast competitor's blades. That beats premature saw replacement and saves you money
- Steam oxide finish no paint to gum up and slow cutting. The saw runs cooler for longerlife and better performance
- Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting
- Made in USA

Specifications

Application : For 2.000 Conduit IN

• Cutting Size: 1-5/8 IN

D Chain : 4

• Hole Diameter: 2-1/2 IN

Material : Bi-Metal

Material Master Number : 50298364

Package: 30/Standard PackPipe Tap Size: 2.000 INType: Variable Pitch

Use With Quick Change Arbor No.: 2801Use With Standard Arbor No.: 37156