

HOLESAW, VARIABLE PITCH (4 1/4) STD PK 10

Bi-Metal Hole Saws

Cat No: 825B-4-1/4

UPC No: 783310380498

Description

• Cut through steel, tin, aluminum, fiberglass, wood and plastic

- Deep 1-5/8 IN (41.3 mm) cutting depth allows for cuttingthrough 2 IN x 4 IN wood studs
- Extra-tough bi-metal bladewe use the highest grade of tool steel to outlast competitor's blades. That beats premature saw replacement and saves you money
- Steam oxide finish no paint to gum up and slow cutting. The saw runs cooler for longerlife and better performance
- Extra-thick backplate minimizes vibration for smoother, easier, less tiring cutting
- Made in USA

Specifications

• Cutting Size: 1-5/8 IN

• D Chain: 4

• Hole Diameter: 4-1/4 IN

Material : Bi-Metal

Material Master Number : 50380494

Package : 10/Standard PackPipe Tap Size : 4.000 IN

1 lpe rap Size : 4.000 li

Type : Variable Pitch

Use With Quick Change Arbor No.: 2801
Use With Standard Arbor No.: 37156