

## CUTTER PKG, HSS 1.375& quot;



Ultra Cutters

Cat No: 925-1-3/8 UPC No: 783310101598

## Description

- Lasts 10 times longer than standard hole saws •
- Precision-ground teeth cut smooth, burr-free holes with ease •
- 1/4 IN (6.35 mm) capacity •
- Durability and speed provide low cost per hole •
- Split-point pilot drill prevents "walking" makes accurate hole placement easy •
- Spring-loaded slug ejector saves time •
- No tool required to change cutter sizes ٠
- Less chance of broken teeth because the saw body is machined out of solid, high-speed steel •

## **Specifications**

- Application : For 1.000 IN Conduit •
- Hole Diameter : 1-3/8 IN •
- Material : High Speed Steel •
- Type : Ultra •