

HDC enclosures HDC 64D TOBO 1PG29G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

General ordering data

Type	HDC 64D TOBO 1PG29G
Order No.	1662100000
Version	HDC enclosures, Size: 8, Protection degree: IP 65, Cable entry from top, Plug housing, Side-locking clamp on upper side, high, Size of cable entries: PG 29
GTIN (EAN)	4008190418625
Qty.	1 pc(s).

HDC enclosures HDC 64D TOBO 1PG29G

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Dimensions and weights

Length	163 mm	Width	55 mm
Height	76 mm	Net weight	387 g

Dimensions

Total length housing	120 mm	Width housing C	43 mm
Height of housing B	76 mm	Cable entry	w. threading

General data

Housing main material	diecast aluminium
-----------------------	-------------------

Version

Internal thread	PG 29	Design of housing	Cable entry from top, Plug housing
Size	8	Design	high
Top part/bottom part/lid	upper part	Design of locking system	Side-locking clamp on upper side
Cable entry	w. threading	Size of cable entries	PG 29
Number of cable entry on top	1	Number of cable entry sideways	0

Classifications

ETIM 2.0	EC000437	ETIM 3.0	EC000437
UNSPSC	30-21-18-01	eClass 4.1	40-02-06-14
eClass 5.1	27-14-34-19	eClass 6.2	27-26-12-03
eClass 7.1	27-44-02-02		

Approvals

Approvals



ROHS Conform

Downloads

DXF	1662100000_HDC_64D_TOBO_1PG29G_STP.dxf
STEP	1662100000_HDC_64D_TOBO_1PG29G_STP.stp
PDF	1662100000_HDC_64D_TOBO_1PG29G_STP_Blatt_1.pdf
IGES	1662100000_HDC_64D_TOBO_1PG29G_STP.igs
VRML	1662100000_HDC_64D_TOBO_1PG29G_STP.vrl
EPLAN	1662100000.MZF

Data sheet...

**HDC enclosures
HDC 64D TOBO 1PG29G**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

