## **Butane-Powered Soldering Irons**

PI-20SiK Professional Soldering Iron Kit



## **Professional Soldering Iron Kit**

Model No.

Description

PI-20SiK

Professional butane soldering iron, flameless heat tool and torch with 4 soldering tips, flameless heat shrink adapter, hot knife tip, lead-free solder, sponge tray, protective cap and case

## **Specifications**

- Adjustable Soldering Temp: 680°F to 820°F (360°C to 438°C)
- Approx Hot Air Temp: 820F (438C)
- **Approx Torch Temp:** 2370F (1300C)
- **Power:** 167 watts max. (16 grams/hour consumption rate)
- Refillable Tank Capacity: 7 ml (0.24 fl oz)

**NOTE:** Users should independently evaluate the suitability of the product for their application.

- Tank Run Time: 60 minutes at low setting, 30 minutes at high setting.
- **Dimensions:** 8.7 inch L (220mm) x 1.08" W (27.5mm) x 1.7" H (43mm)
- Weight: 2.9oz (.18 lb; 82 grams) without fuel
- Shipping Weight: 1.1 lbs
- **Soldering Tips:** Base material copper; gold plating (0.2 0.3 microns)

## PI-20SIK Professional Butane Powered Soldering Iron, Flameless Heat Tool and Torch Kit

- Cordless, portable, lightweight and easy to use
- Self-igniting
- · Open flame function

- Power with Master Ultratane® butane fuel
- Use to shrink electrical connectors, shrink tubing, cordless soldering, light gauge welding, use as an open flame torch and more