



LED VA19-3000cec

Lamp Class: A19 Clear Glass



Product Description

LED VA19-3000cec delivers superior brightness, valuable energy savings and long lasting performance. greater light distribution. This A19 Class LED bulb comes in 3000K CCT (Soft White) for charming and hospitable environments.
















Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
8.5 W	120 V	800 lm	320°	N/A	3000 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
90	94 lm/W	0.7	0.095 A	E26	15,000 Hrs.

Product Features & Benefits



Dimmable



Energy Efficient




Enclosed Fixture Suitable



Wet Rated

Product Dimensions



Product Photometric Data

