Euri Lighting



EFS

Clear Glass

LED VA19-3020cec

Lamp Class: A19 Clear Glass

Product Description

LED VA19-3020cec delivers superior brightness, valuable energy savings and long lasting performance. LED Filaments along with heat-sink absence unmistakably mimic traditional bulb styles while providing greater light distribution. This A19 Class LED bulb comes in 2700K CCT (*Warm White*) for charming and hospitable environments.



*Note: Design, features and specifications subject to change without notice. Some features may not be available on all models. Please visit www.eurilighting.com or call 1-888-743-5766 for more information.

Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
8.5 W	120 V	800 lm	320°	N/A	2700 K

2700K

CCT

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
90	94 lm/W	0.7	0.095 A	E26	15,000 Hrs.

Product Features & Benefits	Product Dimensions	Product Photometric Data
Dimmable	2.36"	
Energy Efficient		
Enclosed Fixture Suitable		CURRENTLY NOT AVAILABLE
Wet Rated		

Euri Lighting | A Division of IRTRONIX Inc.