



LED VA19-3020ef

Lamp Class: A19 Frosted Glass



Product Description


LED VA19-3020ef delivers superior brightness, valuable energy savings and long lasting performance. greater light distribution. This A19 Class LED bulb comes in 2700K CCT (Warm White) for charming and hospitable environments.













Specifications

Input Power	Input Voltage	Lumen Output	Beam Angle	Center Beam	ССТ
8 W	120 V	800 lm	320°	N/A	2700 K

CRI	Luminous Efficacy	Power Factor	Input Current	Base/Cap	Lamp Lifespan
80	100 lm/W	0.7	0.095 A	E26	15,000 Hrs.

Product Features & Benefits

Dimmable



Energy Efficient




Enclosed Fixture Suitable



Wet Rated

Product Dimensions



Product Photometric Data

