


## 500ft CAT 6 Solid STP Outdoor Bulk Ethernet 23AWG Cable with 20pcs of shielded RJ45 connectors TR4-560BLOU-KIT



Our cable allows for maximum performance while minimizing electromagnetic interference/radio-frequency interference (EMI/RFI) and almost eliminating alien crosstalk (AXT).

Suitable for fast, Gigabit, and 10-Gigabit Ethernet and supports bandwidths of up to 550MHz. Packaged in a hassle-free, tangle free, easy pull wooden reel you won't have to worry about getting behind on your next job.

Pure bare copper produces a stronger signal along with better conductivity and flexibility when compared to copper clad aluminum (CCA).

Designed to withstand sunlight, dirt, and moisture.

Rugged and durable for extreme environments.

Bury directly in the ground or use in conduit.

Connect to what matters: computers, printers, gaming consoles, routers, ethernet extenders, switch boxes, VoIP phones, IP cameras, PoE devices, etc. All data cables meet or exceed ANSI TIA/EIA 568-C.2 standards, and are RoHS compliant.

## **Features:**

- Heavy-duty 23 AWG insulated wire
- UV resistant and Waterproof outdoor rated bulk solid wire cable
- Ideal for data, voice and security applications requiring outdoor placement



- Solid bare pure copper conductors for flexibility and less conductor breakage
- Conductor separator spine to fight against twists and kinks to reduce crosstalk for a cleaner signal
- Rip cord to strip PVC cable jacket
- Comes with 20 pcs Shielded Modular Connectors rated for stranded & solid CAT 7/6A/6 cable.