

250 Feet Cat7 Bulk Ethernet 23AWG Cable Solid & Shielded (S/FTP) CMR Riser (Blue) (TR4-580SRBL-250)



Product Overview

CAT7 Bare Copper Solid & Shielded S/FTP (Screened Foiled Twisted Pair) UL Listed for In-Wall and Riser Installation (CMR) ISO/IEC 11801 Verified, RoHS Compliant

Supports up to 600MHz and Suitable for 1000BASE-T / 1000BASE-TX (Gigabit Ethernet) and 10GBASE-T (10-Gigabit Ethernet)

Features:

Application: UL Listed for In-Wall and Riser Installation (CMR)

Conductor: CAT7 Bare Copper 23AWG Solid S/FTP (Shielded & Foiled

Twisted Pair)

Jacket: Blue PVC 7.5 mm in Outside Diameter RoHS Compliant Transfer Rates: 10/100/1000 Mbps up to 600 MHz Bandwidth

Standards: ISO/IEC 11801