

Model	TAO3072	TAO3102	TAO3122	TAO3072A	TAO3102A	TAO3122A
Bandwidth	70MHz	100MHz	120MHz	70MHz	100MHz	120MHz
Sample Rate	1GS/s					
Vertical Resolution (A/D))	8 bits			8bits/12bits/14 bits		
Record length	40M					
Waveform Refresh Rate	75,000 wfms/s					
Horizontal Scale (s/div))	1ns/div - 1000s/div, step by 1 - 2 - 5					
Channel	2					
Display	8" color LCD, 800 x 600 pixels display, multi-touch screen					
Input Impedance	1MΩ ± 2%, in parallel with 15pF ± 5pF					
Max Input Voltage	1MΩ ≤ 300Vrms;					
DC Gain Accuracy	±3%					
Probe Attenuation Factor	0.001X - 1000X, step by 1 - 2 - 5					
Sample Rate / Relay Time Accuracy	±2.5ppm					
Input Coupling	DC, AC, GND					
Vertical Sensitivity	1mV/div - 10V/div (at input)					
Trigger Type	Edge, Video, Pulse, Slope, Runt, Windows, Timeout, Nth Edge, Logic, I2C, SPI, RS232, and CAN (optional)					
Bus Decoding(optional)	I2C, SPI, RS232, CAN					
Trigger Mode	Auto, Normal, and Single					
Automatic Measurement	Vpp, Vavg, Vrms, Freq, Period, Week RMS, Cursor RMS, Vmax, Vmin, Vtop, Vbase, Vamp, Overshoot, Phase A→B ↑, Phase A→B↓, Preshoot, Rise Time, Fall Time, +Width, -Width, +Duty, -Duty, Duty Cycle, Delay A→B ↑, Delay A→B↓, +Pulse Count, -Pulse Count, Rise Edge Count, Edges Count, Area, Cycle Area					
Waveform Math	+, -, ×, ÷, FFT, FFTrms,Intg,Diff,Sqrt, User Defined Function, Digital Filter					
Waveform Storage	100 waveforms					
Communication Interface	USB host, USB device, USB port for PictBridge,LAN, and WIFI (optional)					
Frequency Counter	available					
Battery	7.4V, 8000mAh, 5 hours operation					
Dimension(WxHxD)	270x191x48 (mm)					
Device Weight	About 1.7kg					

+ Multimeter Specifications (only apply for 2 channels model)

Display	Voltage	Current	Impedance	Diode	Auto Ranging
4 1/2 digitals	mV: 20.000mV - 200.00mV DCV: 2.0000V - 1000.0V ACV: 2.0000V - 750.0V	ACD: 20.00A ACA:20.00A	200.00Ω - 100.00MΩ	√	√