


500Ft CAT7 Bulk Ethernet 23AWG Cable Solid & Shielded (S/FTP) CMR Riser (Blue) With 20 pcs of Shielded Modular Connectors (TR4-580SRBL-KIT)



Micro Connectors' Bulk CAT7 Shielded Cable comes on a convenient wooden spool for easy access, providing you with 500 feet of high quality, solid full copper wire with shielded and foiled twisted pair, ready for termination and routing. The braided shield with foiled twisted pair protects your data as it travels through the four twisted pairs of 23-gauge solid copper wires by wrapping it in a thin metal sleeve thus keeping electrical interference from things like fluorescent lights and electrical lines found in a drop ceiling or inside walls at a minimum. Simply pull the length required for your installation straight from the spool and terminate at your leisure. These cables are a great aid in large scale network installations and other long-distance cable runs and like all of our bulk networking cables, these are constructed with only high-quality components that can be counted on for high performance.



Features:

- S/FTP (Braided Shielded & Foiled Twisted Pair) shielding to reduce crosstalk, EMI and electrical interference
- CMR In-Wall Riser rated cable jacket
- CAT7 speeds up to 10Gbps and 600 MHz bandwidth to future proof your installation
- 23 AWG individual solid pure copper conductors
- Supports Power over Ethernet: PoE, PoE+, and PoE++
- Comes on a convenient wooden spool for easy access
- Running "FT" count printed on cable for easy measurement
- Meets ANSI/TIA-568-C specifications and UL, RoHS and TAA compliant

Due to the overall thickness of the shielded bulk cable, some standard RJ45 connectors will not fit properly with this cable. We recommend using our universal CAT 7/6A/6 shielded modular connectors (C20-088L7S-20) or purchase the bundle kit to ensure a correct termination for optimal signal performance

Specifications/Contents: Model: TR4-580SRBL-KIT

Category: CAT 7

Conductor: Solid bare copper

Wire Gauge: 23 AWG

Cable Jacket: CMR In-wall riser rated

Shielding: S/FTP (Braided Shielded & Foiled Twisted Pair)

Color: Blue Length: 500 ft

Overall Cable Outer Diameter: 7.5 mm

Package Includes: 500ft cable and 20 pcs of connectors