

# NTC-S1024A

Analog light controller

- Compact design, flexible for deployment;
- APPLICable to standard lights and spot light;
- Stable output current;
- Easy intensity adjustment.

Model	NTC-S1024A
Power supply	DC 24V
Output	24V 10mA~1A
Channels	1
Accommodation mode	Potentiometer 0~100 (min 0, max 100)
Trigger	/
Operating Environment	Temperature 0°C ~ 40°C, Humidity 25% ~ 85%
Size	51mm*36mm*15mm(L*W*H)
Weight	50g
A patch cord is required when using spot light.	

