


250 Feet CAT 6A Solid & Shielded (F/UTP) CMR Riser Bulk Ethernet Cable with 10-Pack Universal Shielded RJ45 Connectors - Blue (TR4-70SRBL250-K)



Micro Connectors' Bulk CAT6A CMR Riser Shielded Cable comes on a convenient wooden spool for easy access, providing you with 250 feet of high quality, solid full copper wire with overall aluminum foil shielding, ready for termination and routing. The Mylar foil shielding protects your data as it travels through the four twisted pairs of 23-gauge solid copper wires by wrapping it in a thin metal sleeve thus keeping electrical interference from things like fluorescent lights and electrical lines found in a drop ceiling or inside walls at a minimum. Simply pull the length required for your installation straight from the spool and terminate at your leisure. These cables are a great aid in large scale network installations and other long-distance cable runs and like all of our bulk networking cables, these are constructed with only high-quality components that can be counted on for high performance.



Features:

- Overall aluminum foil shielding (F/UTP) CMR In-Wall Riser Rated Category
 6A Ethernet cable
- 23 AWG individual solid pure copper conductors
- Supports Power over Ethernet: PoE, PoE+, and PoE++
- Bandwidth speed up to 750 MHz
- Cross separator spline to ensure better signal performance and less crosstalk
- Comes on a convenient wooden spool for easy access
- Running "FT" count printed on cable for easy measurement
- Meets ANSI/TIA-568-C specifications and UL, RoHS and TAA compliant
- Each package comes with 10 sets of shielded modular connectors

Due to the overall thickness of the shielded bulk cable, some standard RJ45 connectors will not fit properly with this cable. We recommend using our universal CAT 7/6A/6 shielded modular connectors (C20-088L7S-20) or purchase the bundle kit to ensure a correct installation for optimal signal performance

Specifications/Contents: Model: TR4-70SRBL250-K

Category: CAT 6A

Conductor: Solid bare copper

Wire Gauge: 23 AWG

Cable Jacket: CMR In-wall riser rated

Shielding: F/UTP overall aluminum foil shielding

Color: Blue Length: 250 ft

Overall Cable Outer Diameter: 7.0 mm

Package Includes: 250 ft CAT 6A cable and 10 shielded connectors

Weight: 12 lbs