
OD3006-05LSS



DC Fan, 5V 30 x 7mm (1.18" x 0.28")






I I	
Frame	PBT UL94 V-0 Plastic
Impeller	PBT UL94 V-0 Plastic
Connection	2x Wire Leads, 28 AWG
Motor	Brushless DC, Auto Cutoff, Auto Restart, Electronically Protected
Bearing System	Sealed Sleeve
Dielectric Strength	500VAC/min, <1mA
Insulation Resistance	10M ohm between lead wires and frame (500 VDC)

Operating Temperature -10°C ~ +70°C

Storage Temperature -40°C ~ +70°C

<u>Life Expectancy</u> 50,000 hours (L10 at 25°C)

Weight: 0.01 lbs



Part Number	OD3006-05LSS
Rated Voltage	5 VDC
Voltage Range	4.5 ~ 5.5
Input Power	0.45 W
Rated Current	0.09 A
Rated Speed (RPM)	7450
Airflow (CFM)	2.3
Noise Level (dB)	25
Max. Static Pressure	0.09" H ₂ O