



### Material

Screws	M5.0 Steel Zn plated
Pin Header	Copper alloy , Sn plated
Housing	PBT , UL94V-0

### Electrical

Standard	UL
Rated Voltage	600V
Rated current	65A
Wire range	14-6AWG
Contact Resistance	20mΩ
Insulation resistance	1000MΩ/DC500V
Withstanding voltage	AC2500V/1Min

### Other Data

Pitch/Poles [mm]/[P]	16.0/1-15
Operating temperature [°C]	-40°C~+130°C
Torque	25.5Kgf.cm/2.5Nm/22.1Lb.in

Dimensions

PCB opening diagram

