



Material

| | |
|------------|--------------------------|
| Screws | M4.0 Steel Ni plated |
| Pin Header | Copper alloy , Sn plated |
| Housing | PA66 , UL94V-0 |

Electrical

| | | |
|-----------------------|--------------|------------------|
| Standard | UL | IEC |
| Rated Voltage | 300V | 500V |
| Rated current | 20A | 32A |
| Wire range | 22-12AWG | 4mm ² |
| Contact Resistance | 20mΩ | |
| Insulation resistance | 500MΩ/DC500V | |
| Withstanding voltage | AC2000V/1Min | |

Other Data

| | |
|----------------------------|-----------------------------|
| Pitch/Poles [mm]/[P] | 11.0/2-24 |
| Operating temperature [°C] | -40°C~+105°C |
| Torque | 12.24Kgf.cm/1.2Nm/10.6Lb.in |

Dimensions

PCB opening diagram

