

DOODLE LABS 900 MHZ & 2.4 GHZ OMNI ANTENNA

ANT-1700-3-O



ELECTRICAL DATA

Frequency Range	694-960 & 1710-2750 MHz
Peak Gain	3 dBi
VSWR	2:1 max over range
Maximum Power	5 Watts
Impedance	50 ohms nominal

GENERAL DATA

Colour	Black
Radome Material	Polyurethane, with black matt finish, and knurled connector
Connector Type	SMA Male with adjustable right angle elbow
Construction	PVC

DOODLE LABS 900 MHZ & 2.4 GHZ OMNI ANTENNA

ANT-1700-3-O



MECHANICAL DATA

Length	200 mm
Width	17 mm
Mounting Type	Connector
Weight	34 g


ENVIRONMENTAL DATA

Environmental Condition	Indoor/Outdoor
Operation Temperature	-40°C to +85 °C
Storage temperature	-40°C to +85 °C
Transport temperature	-40°C to +85 °C
IP Rating	IP65


DOODLE LABS 900 MHZ & 2.4 GHZ OMNI ANTENNA

ANT-1700-3-O


ELEVATION @ 694 MHz




ELEVATION @ 750 MHz




ELEVATION @ 850 MHz




ELEVATION @ 950 MHz




ELEVATION @ 1710 MHz




ELEVATION @ 1880 MHz




ELEVATION @ 2150 MHz



ELEVATION @ 2450 MHz



ELEVATION @ 2650 MHz




DOODLE LABS 900 MHZ & 2.4 GHZ OMNI ANTENNA


ANT-1700-3-O

Dimension are in mm

SIDE VIEW



FRONT VIEW



SIDE VIEW (TILT 90°)

