

ø 42mm BLDC Motor

3-Phase Brushless

MOT-BL-42S1-24V

Online ID#: BLDC-J42-41-24-5500-01


Our BLDC Motors are a high quality solution providing excellent speed and torque output with superior reliability and control.

With endless performance combinations, we have a fully tailored gear motor solution for you.

Contact Us for alternative solutions!

Specifications	
Motor Type:	Brushless - 8 Pole
Rated Voltage:	24V DC
Rated Speed:	4,000 rpm
Rated Torque:	0.637 kg.cm
Rated Current:	1.8 A
Phase Resistance:	1.8 ohms

No-Load Speed:	5,500 rpm (+/- 10%)
No-Load Current:	< 0.3 A
Back EMF:	4.36 V/krpm
Torque Constant:	0.428 kg.cm/A
Max. Power:	32 W
Termination Style:	Lead Wires (20/26AWG)



Performance Curve 100.00% 35.00 6000.00 5.00 90.00% 30.00 5000.00 80.00% 4.00 25.00 70.00% 4000.00 60.00% 20.00 Speed (rpm) Current (A Power (W) 3.00 50.00% Effecien 3000.00 15.00 40.00% 2.00 2000.00 30.00% 10.00 20.00% 1.00 1000.00 5.00 10.00% 0.00 0.00 0.00% 0.00 0 200 400 600 800 1000 1200 1400 1600 1800 Torque (g-cm)



© 2023 ISL Products International Ltd. Specifications subject to change without notice.

ISL Products International Ltd. • 572 Walt Whitman Rd., Suite 100 • Melville, NY 11747 • T 516-937-3475 • www.islproducts.com