

## Ø 42mm BLDC Motor 3-Phase Brushless

**MOT-BL-42S4-24V** 

Online ID#:

BLDC-J42-100-24-5800-04

Our BLDC Motors are a high quality solution providing excellent speed and torque output with superior reliability and control.

With endless performance combinations, we have a fully tailored gear motor solution for you.



## Contact Us for alternative solutions!

Specifications	
Motor Type:	Brushless - 8 Pole
Rated Voltage:	24V DC
Rated Speed:	4,000 rpm
Rated Torque:	2.5 kg.cm
Rated Current:	6.3 A
Phase Resistance:	0.36 ohms

No-Load Speed:	5,800 rpm (+/- 10%)
No-Load Current:	< 0.8 A
Back EMF:	4.1 V/krpm
Torque Constant:	0.407 kg.cm/A
Max. Power:	113 W
Termination Style:	Lead Wires (20/26AWG)





