

ø52mm Planetary Gear Motor

Carbon - Brushed

MOT-I-81595

Online ID#:


PGM-J52-24-77-67-C

Our Planetary Gear Motors are an inline solution providing excellent torque output at various speeds. They are best for intermittent duty operation. With endless performance combinations, we have a fully tailored gear motor solution for you.


Contact Us for alternative solutions!

Specifications			
Gearhead Type:	Planetary	No-Load Speed:	67 rpm (+/- 10%)
Motor Type:	Carbon - Brushed	No-Load Current:	< 2 A
Rated Voltage:	24V DC	Stall Torque:	* 400 kg.cm
Rated Speed:	55 rpm	Max. Power:	170 W
Rated Torque:	175 kg.cm	Reduction Ratio:	77:1
Rated Current:	9 A	Termination Style:	Lead Wires (18AWG)
* ~ / /			6 :1

* Gearbox limitations are set at 400 kg.cm, operating past this torque limit may create premature failure.



Performance Curve





© 2023 ISL Products International Ltd. Specifications subject to change without notice.