

Technical Data Sheet Rev 05.230616

# ChargeIT Mini 82W USB Type-C PD Charger High w/ 24~48V DC Input

Model Number: CG-PD82HVV



## Features

- Input Voltage Range of 24 ~ 48V DC
- USB Type-C PD with PD 3.0
- PD Profiles: 5V-3A, 9V-3A, 12V-3A, 15V-3A, 20V-4.2A
- BC1.2, Apple Charging, AFC, QC 3.0, 2.0

## Package Contents

- 2-Pin Terminal Block
- Charger

## Specifications

### OVERVIEW

Model No	CG-PD82HVV
Product Type	USB Chargers
Compliance	None or N/A
UPC	045079163751
Country of Origin	China
LED indicators	None or N/A
Chipset	Cypress CCG3PA

### PHYSICAL

Ship Weight (lbs)	0.04 lbs
Ship Weight (kg)	0.02 kg
Item Weight	0.037 lbs lbs
Length	3.48 inches
Width	1.99 inches
Height	1.03 inches
Material	Steel
Color	Black
Mountable	Surface Mount   Wall Mount

## Specifications Cont.

### CONNECTIONS

USB Specification	Charging Only
Maximum Data Rate	N/A
Downstream Port Count	1
Downstream Port Type	1x Type C (Charging)
Works as Standalone Charger	Y - Can be used without Host
Can be Bus Powered	N - External Power Required

### Power

Input Voltage	24~48V DC
Min Input Voltage	22v
Max Input Voltage (DO NOT EXCEED)	55v
Power Connector	Phoenix 2-pin
Idle Power Draw	6 mA @ 24v Terminal Power
Max Power Draw	82w
Max Per Port Draw	4.2A @ 20V (82W) w/ eMarker cable, 3A @ 20V (60w) w/ Standard Cable
Supported Charge Protocols	Apple Charge 2.4A   BC 1.2   DCP   PD   QC 3.0 / 2.0

### ENVIRONMENTAL

Operating Temperature	0C ~ 55C
Storage Temperature	-20C ~ 75C
Operating Humidity	5% to 95% RH

### OS SUPPORT

Supported Operating Systems	OS independent - No software or drivers required
-----------------------------	--

### WARRANTY

Warranty Period	1 Year
-----------------	--------

### PRODUCT URL

CG-PD82HVV Product Page	<a href="https://www.coolgear.com/product/chargeit-mini-82w-usb-type-c-pd-charger-high-w-2448v-dc-input">https://www.coolgear.com/product/chargeit-mini-82w-usb-type-c-pd-charger-high-w-2448v-dc-input</a>
-------------------------	---